


















# 3M™ E-A-Rfit™ Dual-Ear Validation System

## Disposable Foam Test Plugs


Disposable Foam Test Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
E-A-Rsoft™ Yellow Neons™ (regular-sized)	393-2000-50 	<ul style="list-style-type: none"> <li>E-A-Rsoft™ Yellow Neons™</li> <li>E-A-Rsoft™ Yellow Neon™ Blasts™</li> <li>E-A-Rsoft™ SuperFit™</li> <li>Tattoo™</li> <li>Nitro™</li> </ul>	310-1250, Yellow Neons™ Uncorded in Pillow Pak Regular Size 311-1250, Yellow Neons™ Corded in Poly Bag, Regular Size 311-1252, Yellow Neon™ Blasts™ Corded in Poly Bag, Regular Size 311-1254, SuperFit™ Corded in Poly Bag, Regular Size 311-1256, Yellow Neons™ Corded in Poly Bag, Regular Size 311-1257, Yellow Neon™ Blasts™ Corded in Poly Bag, Regular Size 311-4106, Metal Detectable Corded in Poly Bag, Regular Size 311-4109, SuperFit™ Metal Detectable Corded in Poly Bag, Reg Size 311-4110, E-A-Rsoft™ Metal Detectable AV Corded, Poly Bag, Reg Size 312-1250, Yellow Neons™ Uncorded Earplugs in Poly Bag, Reg Size 312-1252, Yellow Neon™ Blasts™ Uncorded in Poly Bag, Reg Size 312-1256, SuperFit™ Uncorded Earplugs in Poly Bag, Reg Size 391-1004, Yellow Neons™ One Touch™ Refill Reg Size 391-1010, Yellow Neon™ Blasts™ One Touch™ Dispens. Refill Reg Size 391-1254, SuperFit™ One Touch™ Refill Regular Size P1000, Nitro™ Earplugs Uncorded P1001, Nitro™ Earplugs Corded P1100, Nitro™ Tattoo™ Earplug Uncorded P1101, Nitro™ Tattoo™ Earplug Corded
E-A-Rsoft™ Yellow Neons Large	393-2014-50 	<ul style="list-style-type: none"> <li>E-A-Rsoft™ Yellow Neons Large</li> </ul>	311-1251, E-A-Rsoft™ Yellow Neons™ Large Corded in Poly bag 312-1251, E-A-Rsoft™ Yellow Neons™ Large Uncorded in Poly bag 312-1255, E-A-Rsoft™ SuperFit™ Large, Uncorded 391-1005, E-A-Rsoft™ Yellow Neons™ Large Uncorded Dispens. Refill
E-A-R™ Classic™	393-2003-50 	<ul style="list-style-type: none"> <li>E-A-R™ Classic™</li> </ul>	310-1001, Uncorded Earplugs in Pillow Pak 310-1060, Uncorded in Pillow Pak 310-1080, Corded Earplugs in Poly Bag 311-1081, Corded Earplugs in Econopack Dispenser Box 311-1101, Corded Earplugs in Poly Bag 312-1080, Uncorded Earplugs in Econopack 312-1082, Uncorded Earplugs in Econopack 312-1201, Uncorded Earplugs in Poly Bag 390-1000, Uncorded Earplugs in Value Pak 391-1001, One Touch™ Refill VP311-1101, Corded Earplugs in 5 PR-100 Pak
E-A-R™ Classic™ Small	393-2007-50 	<ul style="list-style-type: none"> <li>Classic™ Small</li> </ul>	310-1103, Uncorded Earplugs in Pillow Pak 311-1106, Corded Earplugs in Poly Bag 310-4003, Platinum™ Uncorded Earplugs, Poly Bag, 310-1009, SuperFit™ 30 Uncorded Earplugs, in Pillow Pak 312-4201, SuperFit™ 30 Uncorded Earplugs in Poly Bag 311-1126, SuperFit™ 30 Corded Earplugs in Poly Bag 391-1002, SuperFit™ 30 One Touch™ Refill
E-A-R™ Classic™ Plus	393-2009-50 	<ul style="list-style-type: none"> <li>Classic™ Plus</li> </ul>	310-1101, Uncorded Earplugs in Pillow Pak 311-1105, Corded Earplugs in Poly Bag 311-4101, Metal-Detectable Corded Earplugs in Poly Bag 310-1008, SuperFit™ 33 Uncorded Earplugs in Pillow Pak 311-1125, SuperFit™ 33 Corded Earplugs in Poly Bag SF-01-003, SuperFit 36
E-A-R™ Classic™ Soft	Not Available	<ul style="list-style-type: none"> <li>Classic™ Soft</li> </ul>	311-6000 and 311-6001
E-A-R™ TaperFit™ 2	393-2006-50 	<ul style="list-style-type: none"> <li>TaperFit™ 2</li> </ul>	312-1219, Uncorded, Poly Bag, Reg. 312-1223, Corded, Poly Bag, Reg.
E-A-R™ TaperFit™ 2 Large	393-2027-50 	<ul style="list-style-type: none"> <li>TaperFit™ 2 Large</li> </ul>	312-1221, TaperFit™ 2 Earplugs, Uncorded 312-1224, TaperFit™ 2 Earplugs, Corded,
E-A-Rsoft™ FX™	393-2004-50 	<ul style="list-style-type: none"> <li>E-A-Rsoft™ FX™</li> </ul>	312-1260, Corded Earplugs in Poly Bag 2000 PR/Case 312-1261, Uncorded Earplugs in Poly Bag 2000 PR/Case 312-1274, Corded Earplugs in Poly Bag 1000 PR/Case















Disposable Foam Test Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
E-A-R™ E-Z-fit™	393-2005-50 	<ul style="list-style-type: none"> <li>E-A-R™ E-Z-Fit™</li> </ul>	312-1208, Uncorded Earplugs in Poly Bag 2000 PR/Case 312-1222, Corded Earplugs in Poly Bag 2000 PR/Case
E-A-Rsoft™ Grippers	393-2021-50 	<ul style="list-style-type: none"> <li>E-A-Rsoft™ Grip-pers</li> </ul>	312-6001, E-A-Rsoft™ Grippers Corded Earplugs, in Polybag
1100	393-2010-50 	<ul style="list-style-type: none"> <li>3M™ 1100</li> <li>3M™ 1110</li> </ul>	1100, Uncorded Foam Earplugs in Poly Bag 1000 PR/Case 1110, Corded Foam Earplugs in Poly Bag 500 PR/Case





## Push-to-Fit Probed Test Plugs

Push-to-Fit Probed Test Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
E-A-R™ Push-Ins™	393-2002-50 	<ul style="list-style-type: none"> <li>Push-Ins™</li> </ul>	318-1000, Uncorded Earplugs in Poly Bag 318-1001, Corded Earplugs in Poly Bag 318-1002, Uncorded Earplugs in Poly Bag 318-1003, Corded Earplugs in Poly Bag 318-1004, Uncorded Earplugs in Poly Bag 318-1005, Corded Earplugs in Poly Bag 318-3000, Metal Detectable
E-A-R™ Skull Screws™	393-2012-50 	<ul style="list-style-type: none"> <li>Skull Screws™</li> </ul>	P1300, Uncorded Earplugs in Poly Bag P1301, Corded Earplugs in Poly Bag
Push-Ins™ with Grip Rings	393-2015-50 	<ul style="list-style-type: none"> <li>Push-Ins™ with Grip Rings</li> </ul>	318-1009, Push-Ins™ with Grip Rings Corded in Poly bag 318-1008, E-A-R™ Push-Ins™ with Grip Rings Uncorded, Poly bag
No Touch™ Probed	393-2013-50 	<ul style="list-style-type: none"> <li>No Touch™</li> </ul>	P2000, Uncorded in Poly Bag P2001, Corded in Poly Bag
E-A-R™ Express™ Pod Plugs™	393-2008-50 	<ul style="list-style-type: none"> <li>Express™ Pod Plugs™</li> </ul>	321-2100, Blue Grips in Pillow Pak 321-2200, Assorted Color Grips in Pillow Pak 311-1114, Corded Blue Grips in Pillow Pak 311-1115, Corded Assorted Grips in Pillow Pak 311-1127, Corded Metal-Detectable Earplugs in Pillow Pak
E-A-R™ Flexible Fit HA Earplugs	393-2026-50 	<ul style="list-style-type: none"> <li>Flexible Fit</li> </ul>	328-1000, E-A-R™ Flexible Fit HA Uncorded in Polybag 328-1001, E-A-R™ Flexible Fit HA Corded in Polybag
Push-Ins™ SofTouch™	Not available		318-4000, 318-4001, E-A-R™ Push-Ins™ SofTouch™
Pistonz™	Not available		P1400, P1401, P1401A, Pistonz™
UltraFit™ 27	Not available		340-8001, 340-8002


## Reusable Probed Test Plugs


Reusable Probed Test Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
E-A-R™ UltraFit™ Probed	393-2001-50 	<ul style="list-style-type: none"> <li>E-A-R™ UltraFit™</li> <li>E-A-R™ Tracer™</li> </ul>	340-4001, Uncorded Earplugs in Carrying Case 340-4002, Corded Earplugs in Carrying Case 340-4003, Uncorded Earplugs in Poly Bag 340-4004, Corded Earplugs in Poly Bag 340-4007, Metal Detectable Corded Earplugs in Poly Bag 340-4014, Corded Earplugs in Econopack 340-4036, with Cotton Cord in Poly Bag 340-4044, with Cloth Cord in Paper Envelope 340-4017, Metal Detectable Corded Earplugs in Econopack TR-01-000, Tracer™ Metal Detectable Corded Earplugs VP340-4004, Corded Earplugs in 5 PR-100 Pak UF-01-012, UltraFit 20 UF-01-015, UltraFit 14



Reusable Probed Test Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
Tri-Flange™ Probed	393-2011-50 	<ul style="list-style-type: none"> <li>Tri-Flange™</li> <li>E-A-R™ UltraFit Plus™</li> </ul>	P3000, Vinyl Corded Earplugs in Poly Bag P3001, Cloth Corded Earplugs in Poly Bag 340-6004, UltraFit Plus™ Corded Earplugs in Poly Bag 340-6002, UltraFit Plus™ Corded Earplugs in Carrying Case
Reusable 1260	393-2016-50 	<ul style="list-style-type: none"> <li>1260</li> </ul>	1260, Reusable Earplugs, uncorded 1270, Reusable Earplugs, corded 1271, Reusable Earplugs, corded with carry case
UltraFit™ Silicone & Pump Plus	393-2017-50 	<ul style="list-style-type: none"> <li>UltraFit™ Silicone</li> </ul>	Pump Plus 340-3002, 3M™ UltraFit™ Silicone Corded Earplugs, One Size
Pump Millennium Small	393-2023S-50 	<ul style="list-style-type: none"> <li>Pump Millennium</li> </ul>	3M™ Pump Millennium Small
Pump Millennium Med	393-2023M-50 	<ul style="list-style-type: none"> <li>Pump Millennium</li> </ul>	3M™ Pump Millennium Medium <b>Not available:</b> 1241 Reusable Earplugs
Pump Millennium Lg	393-2023L-50 	<ul style="list-style-type: none"> <li>Pump Millennium</li> </ul>	3M™ Pump Millennium Large
Reusable 1290	393-2024-50 	<ul style="list-style-type: none"> <li>Reusable 1290</li> </ul>	3M™ Reusable 1290, 1291, 1292, 1293
TEP/LEP/EEP	393-2030-50 	<ul style="list-style-type: none"> <li>Skull Screws/ Torque™ (regular and metal detectable)</li> </ul>	The following products fitted with this tip: TEP-100/200, LEP-100/200, LEP-200 OR, EEP-100, EEP-100 OR
	393-2031-50 	<ul style="list-style-type: none"> <li>CCC-GRM-25</li> </ul>	The following products fitted with this tip: TEP-100/200, LEP-100/200, LEP-200 OR, EEP-100, EEP-100 OR
	393-2032-50 	<ul style="list-style-type: none"> <li>UltraFit™ Small</li> </ul>	The following products fitted with this tip: TEP-100/200, LEP-100/200, LEP-200 OR, EEP-100, EEP-100 OR
	393-2033-50 	<ul style="list-style-type: none"> <li>UltraFit™ MED</li> </ul>	The following products fitted with this tip: TEP-100/200, LEP-100/200, LEP-200 OR, EEP-100, EEP-100 OR
	393-2034-50 	<ul style="list-style-type: none"> <li>UltraFit™ Large</li> </ul>	The following products fitted with this tip: TEP-100/200, LEP-100/200, LEP-200 OR, EEP-100, EEP-100 OR
Combat Arms™ 4.0 – SMALL	393-2018S-50 	<ul style="list-style-type: none"> <li>Combat Arms™</li> </ul>	370-1030, 3M™ Combat Arms™ Single Tip Corded Earplugs Small
Combat Arms™ 4.0 – MED	393-2018M-50 	<ul style="list-style-type: none"> <li>Combat Arms™</li> </ul>	370-1031, 3M™ Combat Arms™ Single Tip Corded Earplugs Medium

Reusable Probed Test Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
Combat Arms™ 4.0 – LARGE	393-2018L-50 	<ul style="list-style-type: none"> <li>• Combat Arms™</li> </ul>	370-1032, 3M™ Combat Arms™ Single Tip Corded Earplugs Large
Combat Arms™ 4.1 – SMALL	393-2022S-50 	<ul style="list-style-type: none"> <li>• Combat Arms™</li> </ul>	370-1040, 3M™ Combat Arms™ 4.1 Hear-Through Earplugs, 28 dB, Single Ended, Small
Combat Arms™ 4.1 – MED	393-2022M-50 	<ul style="list-style-type: none"> <li>• Combat Arms™</li> </ul>	370-1041, 3M™ Combat Arms™ 4.1 Hear-Through Earplugs, 28 dB, Single Ended, Medium
Combat Arms™ 4.1 – LARGE	393-2022L-50 	<ul style="list-style-type: none"> <li>• Combat Arms™</li> </ul>	370-1042, 3M™ Combat Arms™ 4.1 Hear-Through Earplugs, 28 dB, Single Ended, Large


## Probed Test Cushions

Probed Test Cushions	Probed Test Cushion SKU	Brand Names	Crossover Product SKUs and Descriptions
PELTOR™ Ear-muff Test Cushion A	393-3004-2 	Earmuffs: <ul style="list-style-type: none"> <li>• Optime™ 105</li> <li>• Optime™ III</li> </ul>	H10A, 3M™ PELTOR™ Optime™ 105 Earmuffs, Other-the-head H10P3E, 3M™ PELTOR™ Optime™ 105 Earmuffs, Hard Hat Attached H10B, PELTOR™ Optime 105 Neckband Earmuffs H540A, PELTOR™ Optime III Over-the-head Earmuffs (Bulls Eye III) H540B, PELTOR™ Optime III Neckband Earmuffs H540P3E, PELTOR™ Optime III Hard Hat Attached Earmuffs

Probed Test Cushions	Probed Test Cushion SKU	Brand Names	Crossover Product SKUs and Descriptions
<p>PELTOR™ Ear-muffs X1/X2 Test Cushions B</p>	<p>393-3001-2</p> 	<p>Earmuffs:</p> <ul style="list-style-type: none"> <li>● X1, X2</li> <li>● Optime™ 95</li> <li>● Optime™ 98</li> <li>● Optime™ 101</li> <li>● Optime™ I</li> <li>● Optime™ II</li> <li>● LiteCom</li> <li>● LiteCom Plus</li> </ul> <p>Headsets:</p> <ul style="list-style-type: none"> <li>● LiteCom</li> <li>● LiteCom Plus</li> <li>● ComTac™</li> <li>● AM/FM™</li> <li>● ProTac</li> <li>● CH-3</li> </ul>	<p><b>X-Series and Optime Earmuffs:</b>  X1A, PELTOR™ Over-the-Head  X1B, PELTOR™ Neckband  X1P3E, PELTOR™ Hard Hat-Attached X1P5E &amp;  X1P5E-OR Hard Hat-Attached  X1P51E, PELTOR™ Hard Hat Attached, Wide Brim  X2A, PELTOR™ Over-the-Head  X2B, PELTOR™ Neckband  X2P3E, PELTOR™ Hard Hat-Attached  X2P5E Hard Hat-Attached  H31A, PELTOR™ Hi-Viz Earmuffs  H31P3E, PELTOR™ Hi-Viz Earmuffs  H510A, PELTOR™ Optime I Over-the-head  H510F, PELTOR™ Optime I Folding  H510B, PELTOR™ Optime I Neckband  H510P3E &amp; P3GS, PELTOR™ Optime I Hard Hat Attached  H520A, PELTOR™ Optime II Over-the-head  H520F, PELTOR™ Optime II Folding  H520FHV, PELTOR™ Optime II Folding  H520B, PELTOR™ Optime II Neckband  H520P3E &amp; P3GS, PELTOR™ Optime II Hard Hat Attached  H6B, PELTOR™ Optime 95 Neckband  H6A, PELTOR™ Optime™ 95, Over-the-head  H6P3E, PELTOR™ Optime™ 95, Hard Hat Attached  H7A, PELTOR™ Optime™ 101, Other-the-head  H7B, PELTOR™ Optime 101 Neckband  H7P3E, PELTOR™ Optime™ 101, Hard Hat Attached  H9A, PELTOR™ Optime™ 98, Over-the-head  H9P3E, PELTOR™ Optime™ 98, Hard Hat Attached</p> <p><b>LiteCom Headsets:</b>  LiteCom BRS 2-way radio, Hard hat, MT53H7P3E4600  LiteCom BRS 2-way radio, Headband, MT53H7A4600  LiteCom FRS/BRS, Hard hat, MT53H7P3E4602-NA  LiteCom FRS/BRS, Headband &amp; Neckband, MT53H7A4602-NA  LiteCom Plus Yellow, Hard Hat Attach (Foam &amp; Gel Cushions), MT73H7P3E4410EU  LiteCom Plus Yellow, Headband (Foam &amp; Gel Cushions), MT73H7A4410EU  LiteCom Plus Yellow, Neckband (Foam &amp; Gel Cushions), MT73H7B4610NA  LiteCom Plus, Hard hat, MT7H7P3E4610-NA  LiteCom Plus, Headband, MT7H7A4610-NA  WST™ LiteCom Plus, Hard Hat Attach (Foam &amp; Gel Cushions), MT73H7P3E4610WS6NA  WST™ LiteCom Plus, Headband (Foam &amp; Gel Cushions), MT73H7A4610WS6NA  WST™ LiteCom Plus, M-300 VersaFlo Attached (Foam &amp; Gel Cushions), 7100204418  WST™ LiteCom Plus, Neckband (Foam &amp; Gel Cushions), MT73H7B4610WS6NA  WST™ LiteCom PRO III Headset - Hard Hat, MT73H7P3E4D10  WST™ LiteCom PRO III Headset - Headband, MT73H7A4D10  WST™ LiteCom PRO III Headset - Neckband, MT73H7B4D10  WST™ LiteCom PRO III Headset IS, Hard hat, MT73H7P3E4D10NA-50  WST™ LiteCom PRO III Headset IS, Headband &amp; Neckband, MT73H7B4D10NA-50  WST™ LiteCom PRO III, M-300 VersaFlo Attached (Foam Cushions), UU008027839</p> <p><b>ComTac Headsets:</b>  ComTac™ XPI Folding band, Foam &amp; Gel Cushions, MT20H682FB  ComTac™ VI w/ NIB Folding band, Foam Cushions, MT20H682FBN  ComTac™ V, Folding band Gel cushions, AS Patriot 92  ComTac™ V Folding band, Foam &amp; Gel Cushions, MT20H682FB  ComTac™ VI w/NIB Folding band, Foam &amp; Gel Cushions, MT20H682FB  ComTac™ VI Neckband, Foam &amp; Gel Cushions, MT20H682BB  ComTac™ VII Headset, Headband, Foam &amp; Gel Cushions, MT14H41A-300*</p> <p><b>AM/FM Headsets:</b>  Alert™ FM Headband, M2RX7A2-01  Alert™ FM Hard Hat Attached, M2RX7P3E2-01  WST™ Alert™ XP Headband, MRX21A2WS6  WST™ Alert™ XP Hard Hat Attached, M2RX21A3WS6  WST™Alert™ XPI, Blue, Headband  WST™ Alert™ XPI, Yellow, Headband, M2RX21A3WS6-AZ  WorkTunes™ Pro AM/FM Headband, HRXS221A  WorkTunes™ ProAM/FM, Hard Hat Attached, HRXS221P3E  WST™ ProTac XPI FLX2 Neckband, Foam or Gel, MT15H7BWS6-111</p>

Probed Test Cushions	Probed Test Cushion SKU	Brand Names	Crossover Product SKUs and Descriptions
			<p><b>ProTac Headsets:</b>                      ProTac III Slim Headband, MT13H220A                      ProTac III Slim Hard Hat Attached, MT13H220P3E                      ProTac III Headband, MT13H221A                      ProTac III Hard Hat Attached, MT13H221P3E                      WSTM ProTac XPI Headband, Foam or Gel MT15H7P3EWS6,                      WSTM ProTac XPI HardHat Attached, Foam or Gel, MT15H7AWS6-111                      WSTM ProTac XPI FLX2 Headband &amp; Hard Hat, Foam or Gel, MT15H7P3EWS6-111                      WSTM ProTac XPI FLX2 Neckband, Foam or Gel, MT15H7BWS6-111</p> <p><b>2-Way Wired Headsets:</b>                      CH-3 FLX2 Headset, Headband                      CH-3 FLX2 Headset, Neckband                      CH-3 FLX2 Headset, Hard Hat Attached                      CH-3 FLX2 Headset with PTT, Headband                      CH-3 FLX2 Headset with PTT, Neckband                      CH-3 FLX2 Headset with PTT, Hard Hat Attached                      CH-3 FLX2 Listen Only, Headband                      CH-3 FLX2 Listen Only, Neckband                      CH-3 FLX2 Listen Only, Hard Hat Attached                      CH-3 ATEX Listen Only, Headband, HT52A-112-50                      CH-3 ATEX Listen Only, Helmet Attached, HT52P3E-112-50                      3M™ PELTOR™ Twin Cup Headset, ATEX, Helmet Attach (Foam Cushions)</p>
PELTOR™ Ear-muffs X3 Test Cushions C	393-3003-2 	Earmuffs: • X3	X3A, PELTOR™ Over-the-Head X3B, PELTOR™ Neckband <sup>1</sup> X3P3E, PELTOR™ Hard Hat-Attached X3P5E Hard Hat-Attached
PELTOR™ Ear-muffs X4/X5 Test Cushions D	393-3005-2 	Earmuffs: • X4, X5  Headsets • CH-5	X4A, PELTOR™ Over-the-Head X4B, PELTOR™ Neckband <sup>1</sup> X4P3E, PELTOR™ Hard Hat-Attached X4P5E & X4P5E-OR, Hard Hat-Attached X4P5IE, PELTOR™ Hard Hat Attached, Wide Brim X5A, PELTOR™ Over-the-Head X5B, PELTOR™ Neckband <sup>1</sup> X5P3E, PELTOR™ Hard Hat-Attached X5P5E, Hard Hat-Attached CH-5, PELTOR™ High Attenuation Headset, Over-The-Head CH-5, PELTOR™ High Attenuation Headset, Hard Hat-Attached

## Banded Hearing Protectors

Banded Hearing Protectors	Banded Hearing Protectors SKU	Brand Names	Crossover Product SKUs and Descriptions
EARcaps™ Model 200	393-2020-50 	Banded Hearing Protector: *E-A-R Caps™	321-2101, E-A-R Caps™ Model 200 Hearing Protector 321-2103, Replacement Pods for E-A-R Caps™ Model 200

### NOTES:

1) E-A-Rfit™ can only be used to fit test the specific 3M hearing protectors listed in the Crossover Product column using the corresponding test probe. E-A-Rfit™ test results are not valid for any other 3M or non-3M hearing protectors.

2) If the earmuffs are worn in conjunction with a liftable visor, the visor should be in the up position when fit testing.

\* The probed test cushions for X3B, X4B and X5B neckband earmuffs do not include the looped back plate, which is needed to attach the head strap for valid fit test results. The looped plate should be temporarily removed from the test subject's regular cushions and attached to the probed cushions as shown for fit testing with the headstrap.

\*\* Remove gray back plate from the probed test cushion when fit testing all CH-3 headsets.



Abadis AG · Sihlbruggstrasse 144 · CH-6340 Baar  
Tel. 041 768 27 27 · Fax 041 768 27 20 · [info@abadis.ch](mailto:info@abadis.ch)

**Besuchen Sie unseren E-Shop mit über 3'000 Artikeln  
unter [www.abadis.ch](http://www.abadis.ch)**